

# Get Fast Identification with B-494 Color Polyester Labels



Properly identifying samples is an important step in any successful lab project. While there are a variety of identification options available, they can be clumsy, time consuming or can't survive the harshest lab environments. With B-494 Color Polyester Labels from Brady, you get the quick visual differentiation you need between samples.

This B-494 material is designed to withstand the harshest lab environments, including liquid nitrogen, a variety of chemicals and more. And, with the ability to print on these labels through a variety of desktop and portable Brady printers, you can get easy-to-read identification, as well as:

- 6 color options that allow you to distinguish many different samples
- Custom options to fit your process and glassware needs
- Efficient label creation when you add the Brady Workstation Laboratory Identification Software Suite

## B-494 Color Polyester Labels

Fits Printer	Diagram	Catalog #	Color	Label Width A	Label Height B	Secondary Label C Diameter	Labels Per Row	Labels Per Roll	Rec. Ribbon Series
For use with the BMP®51 Label Printer									
BMP51	Fig. 24	M-118-494-BL	Blue	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 24	M-120-494-BL	Blue	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 2	M-131-494-BL	Blue	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	180	R6400
BMP51	Fig. 2	M-49-494-BL	Blue	1 in. (25.4 mm)	1 in. (25.4 mm)		1	260	R6400
BMP51	Fig. 24	M-118-494-GN	Green	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 24	M-120-494-GN	Green	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 2	M-131-494-GN	Green	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	180	R6400
BMP51	Fig. 2	M-49-494-GN	Green	1 in. (25.4 mm)	1 in. (25.4 mm)		1	260	R6400
BMP51	Fig. 24	M-118-494-OR	Orange	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 24	M-120-494-OR	Orange	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 2	M-131-494-OR	Orange	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	180	R6400
BMP51	Fig. 2	M-49-494-OR	Orange	1 in. (25.4 mm)	1 in. (25.4 mm)		1	260	R6400
BMP51	Fig. 24	M-118-494-PK	Pink	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 24	M-120-494-PK	Pink	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 2	M-131-494-PK	Pink	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	180	R6400
BMP51	Fig. 2	M-49-494-PK	Pink	1 in. (25.4 mm)	1 in. (25.4 mm)		1	260	R6400
BMP51	Fig. 24	M-118-494-RD	Red	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	250	R6400
BMP51	Fig. 24	M-120-494-RD	Red	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 2	M-131-494-RD	Red	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	180	R6400
BMP51	Fig. 2	M-49-494-RD	Red	1 in. (25.4 mm)	1 in. (25.4 mm)		1	260	R6400
BMP51	Fig. 24	M-118-494-YL	Yellow	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 24	M-120-494-YL	Yellow	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	240	R6400
BMP51	Fig. 2	M-131-494-YL	Yellow	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	180	R6400
BMP51	Fig. 2	M-49-494-YL	Yellow	1 in. (25.4 mm)	1 in. (25.4 mm)		1	260	R6400




Figure 2




Figure 24




Figure 25

## B-494 Color Polyester Labels (cont.)

Fits Printer	Diagram	Catalog #	Color	Label Width A	Label Height B	Secondary Label C Diameter	Labels Per Row	Labels Per Roll	Rec. Ribbon Series
<b>For use with the BMP®61 Label Printer</b>									
BMP61	Fig. 24	M61-98-494-BL	Blue	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	500	R6400
BMP61	Fig. 2	M61-17-494-BL	Blue	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	500	R6400
BMP61	Fig. 2	M61-19-494-BL	Blue	1 in. (25.4 mm)	1 in. (25.4 mm)		1	250	R6400
BMP61	Fig. 24	M61-98-494-GN	Green	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	500	R6400
BMP61	Fig. 2	M61-17-494-GN	Green	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	500	R6400
BMP61	Fig. 2	M61-19-494-GN	Green	1 in. (25.4 mm)	1 in. (25.4 mm)		1	250	R6400
BMP61	Fig. 24	M61-98-494-OR	Orange	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	500	R6400
BMP61	Fig. 2	M61-17-494-OR	Orange	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	500	R6400
BMP61	Fig. 2	M61-19-494-OR	Orange	1 in. (25.4 mm)	1 in. (25.4 mm)		1	250	R6400
BMP61	Fig. 24	M61-98-494-PK	Pink	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	500	R6400
BMP61	Fig. 2	M61-17-494-PK	Pink	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	500	R6400
BMP61	Fig. 2	M61-19-494-PK	Pink	1 in. (25.4 mm)	1 in. (25.4 mm)		1	250	R6400
BMP61	Fig. 24	M61-98-494-RD	Red	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	500	R6400
BMP61	Fig. 2	M61-17-494-RD	Red	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	500	R6400
BMP61	Fig. 2	M61-19-494-RD	Red	1 in. (25.4 mm)	1 in. (25.4 mm)		1	250	R6400
BMP61	Fig. 24	M61-98-494-YL	Yellow	1 in. (25.4 mm)	0.375 in. (9.5 mm)	0.375 in. (9.5 mm)	1	500	R6400
BMP61	Fig. 2	M61-17-494-YL	Yellow	1 in. (25.4 mm)	0.5 in. (12.7 mm)		1	500	R6400
BMP61	Fig. 2	M61-19-494-YL	Yellow	1 in. (25.4 mm)	1 in. (25.4 mm)		1	250	R6400
<b>For use with the BBP®33 Label Printer</b>									
BBP33	Fig. 25	B33-152-494-BL	Blue	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	1500	R6400
BBP33	Fig. 24	B33-250-494-BL	Blue	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	1500	R6400
BBP33	Fig. 2	B33-179-494-BL	Blue	1 in. (25.4 mm)	1 in. (25.4 mm)		1	1500	R6400
BBP33	Fig. 25	B33-152-494-GN	Green	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	1500	R6400
BBP33	Fig. 24	B33-250-494-GN	Green	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	1500	R6400
BBP33	Fig. 2	B33-179-494-GN	Green	1 in. (25.4 mm)	1 in. (25.4 mm)		1	1500	R6400
BBP33	Fig. 25	B33-152-494-OR	Orange	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	1500	R6400
BBP33	Fig. 24	B33-250-494-OR	Orange	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	1500	R6400
BBP33	Fig. 2	B33-179-494-OR	Orange	1 in. (25.4 mm)	1 in. (25.4 mm)		1	1500	R6400
BBP33	Fig. 25	B33-152-494-PK	Pink	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	1500	R6400
BBP33	Fig. 24	B33-250-494-PK	Pink	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	1500	R6400
BBP33	Fig. 2	B33-179-494-PK	Pink	1 in. (25.4 mm)	1 in. (25.4 mm)		1	1500	R6400
BBP33	Fig. 25	B33-152-494-RD	Red	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	1500	R6400
BBP33	Fig. 24	B33-250-494-RD	Red	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	1500	R6400
BBP33	Fig. 2	B33-179-494-RD	Red	1 in. (25.4 mm)	1 in. (25.4 mm)		1	1500	R6400
BBP33	Fig. 25	B33-152-494-YL	Yellow	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	1500	R6400
BBP33	Fig. 24	B33-250-494-YL	Yellow	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	1500	R6400
BBP33	Fig. 2	B33-179-494-YL	Yellow	1 in. (25.4 mm)	1 in. (25.4 mm)		1	1500	R6400
<b>For use with the BradyPrinter i5100, i7100, IP and PR Plus Printers</b>									
THT	Fig. 25	THT-152-494-BL	Blue	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	3000	R6400
THT	Fig. 24	THT-250-494-BL	Blue	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	3000	R6400
THT	Fig. 2	THT-179-494-BL	Blue	1 in. (25.4 mm)	1 in. (25.4 mm)		1	3000	R6400
THT	Fig. 25	THT-152-494-GN	Green	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	3000	R6400
THT	Fig. 24	THT-250-494-GN	Green	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	3000	R6400
THT	Fig. 2	THT-179-494-GN	Green	1 in. (25.4 mm)	1 in. (25.4 mm)		1	3000	R6400
THT	Fig. 25	THT-152-494-OR	Orange	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	3000	R6400
THT	Fig. 24	THT-250-494-OR	Orange	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	3000	R6400
THT	Fig. 2	THT-179-494-OR	Orange	1 in. (25.4 mm)	1 in. (25.4 mm)		1	3000	R6400
THT	Fig. 25	THT-152-494-PK	Pink	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	3000	R6400
THT	Fig. 24	THT-250-494-PK	Pink	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	3000	R6400
THT	Fig. 2	THT-179-494-PK	Pink	1 in. (25.4 mm)	1 in. (25.4 mm)		1	3000	R6400
THT	Fig. 25	THT-152-494-RD	Red	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	3000	R6400
THT	Fig. 24	THT-250-494-RD	Red	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	3000	R6400
THT	Fig. 2	THT-179-494-RD	Red	1 in. (25.4 mm)	1 in. (25.4 mm)		1	3000	R6400
THT	Fig. 25	THT-152-494-YL	Yellow	1 in. (25.4 mm)	0.375 in. (9.5 mm)		2	3000	R6400
THT	Fig. 24	THT-250-494-YL	Yellow	1 in. (25.4 mm)	0.5 in. (12.7 mm)	0.375 in. (9.5 mm)	1	3000	R6400
THT	Fig. 2	THT-179-494-YL	Yellow	1 in. (25.4 mm)	1 in. (25.4 mm)		1	3000	R6400




Figure 2




Figure 24




Figure 25

▶ For more information, visit [BradyID.com](http://BradyID.com)

USA  
Customer Service: 1-888-272-3946  
Inside Sales: 1-888-311-0775  
[BradyID.com](http://BradyID.com)

Canada  
Customer Service: 1-800-263-6179  
[BradyCanada.ca](http://BradyCanada.ca)

Mexico  
Customer Service: 1-800-262-7777  
Inside Sales: 1-800-262-7777 ext 177  
[BradyLatinAmerica.com](http://BradyLatinAmerica.com)

